

Rubber Compounding Materials FT-IR Spectral Library

Index of Compounds

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
0001	3M DYNAMAR	0060	AKROCHEM ZPD POWDER
0002	3M PPA-790	0061	ALCO ALCOSPHERE L-15
0003	3M PPA-791	0062	ALCO ALCOSPHERE 104
0004	AKROCHEM 70 TBPA	0063	ALCO ALCOSPHERE 149
0005	AKROCHEM ACCELERATOR 40B LIQUID	0064	ALCO AQUATREAT AR-232
0006	AKROCHEM ACCELERATOR BZX PO	0065	ARIZONA ACINTOL DR-22
0007	AKROCHEM ACCELERATOR CRA G	0066	ARIZONA ACINTOL DR-24
0008	AKROCHEM ACCELERATOR MF POWDER	0067	ARIZONA ACINTOL DR-25
0009	AKROCHEM ACCELERATOR MZX POWDER	0068	ARMAK KESSCO BUTYL OLEATE
0010	AKROCHEM ACCELERATOR R POWDER	0069	BORGWARNER EBS WAX
0011	AKROCHEM ACCELERATOR THIO-1	0070	BORGWARNER NONYLPHENOL
0012	AKROCHEM ACCELERATOR VS POWDER	0071	BORGWARNER ULTRANOX 226
0013	AKROCHEM AKROWAX 130	0072	BORGWARNER ULTRANOX 236
0014	AKROCHEM ANTIOXIDANT 12	0073	BORGWARNER ULTRANOX 246
0015	AKROCHEM ANTIOXIDANT 235 POWDER	0074	BORGWARNER ULTRANOX 257
0016	AKROCHEM ANTIOXIDANT 250 POWDER	0075	BORGWARNER ULTRANOX 276
0017	AKROCHEM ANTIOXIDANT 33 POWDER	0076	BORGWARNER ULTRANOX 626
0018	AKROCHEM ANTIOXIDANT 36 POWDER	0077	BORGWARNER WESTON 430
0019	AKROCHEM ANTIOXIDANT 51	0078	BORGWARNER WESTON 494
0020	AKROCHEM ANTIOXIDANT 58 POWDER	0079	BORGWARNER WESTON 600
0021	AKROCHEM ANTIOXIDANT 60 POWDER	0080	BORGWARNER WESTON 619 FLAKE
0022	AKROCHEM ANTIOXIDANT DQ POWDER	0081	BORGWARNER WESTON 626
0023	AKROCHEM ANTIOXIDANT PANA FLAKES	0082	BORGWARNER WESTON 63
0024	AKROCHEM ANTIOXIDANT POSDA	0083	BORGWARNER WESTON DHOP
0025	AKROCHEM ANTIOZONANT E-9604 POWDER	0084	BORGWARNER WESTON DPDP
0026	AKROCHEM ANTIOZONANT MPD-100 FLAK	0085	BORGWARNER WESTON DPP
0027	AKROCHEM ANTIOZONANT PD-1 FLAKES	0086	BORGWARNER WESTON ODPP
0028	AKROCHEM ANTIOZONANT PD-2 LUMPS	0087	BORGWARNER WESTON PDDP
0029	AKROCHEM BBTS POWDER	0088	BORGWARNER WESTON TDP
0030	AKROCHEM BIBBS PELLETS	0089	BORGWARNER WESTON THOP
0031	AKROCHEM BISMET POWDER	0090	BORGWARNER WESTON TIOP
0032	AKROCHEM CBTS (POWDER)	0091	BORGWARNER WESTON TLP
0033	AKROCHEM CURE-RITE 18 POWDER	0092	BORGWARNER WESTON TLTP
0034	AKROCHEM CZ-1	0093	BORGWARNER WESTON TNPP
0035	AKROCHEM DC-40P	0094	BORGWARNER WESTON TPP
0036	AKROCHEM DCBS GRANULES	0095	C. P. HALL BUTYL STEARATE C-895
0037	AKROCHEM DOTG POWDER	0096	C. P. HALL CPH-211-N
0038	AKROCHEM DPG POWDER	0097	C. P. HALL CPH-30-N (PEG 400 MONO
0039	AKROCHEM DPTT POWDER	0098	C. P. HALL CPH-46-N
0040	AKROCHEM MBT POWDER	0099	C. P. HALL DIALLYL PHYHLATE
0041	AKROCHEM NIBUD FLAKES	0100	C. P. HALL MONOPLEX NODA
0042	AKROCHEM NOVOR 924 POWDER	0101	C. P. HALL MONOPLEX S-73
0043	AKROCHEM OBTS FLAKES	0102	C. P. HALL MONOPLEX S-75
0044	AKROCHEM P-86 RESIN	0103	C. P. HALL PARAPLEX G-25
0045	AKROCHEM PEPTIZER 9344 POWDER	0104	C. P. HALL PARAPLEX G-30
0046	AKROCHEM PEPTIZER 9349 POWDER	0105	C. P. HALL PARAPLEX G-31
0047	AKROCHEM PEPTIZER P.P.D. POWDER	0106	C. P. HALL PARAPLEX G-40
0048	AKROCHEM RETARDER AK POWDER	0107	C. P. HALL PARAPLEX G-41
0049	AKROCHEM RETARDER PX POWDER	0108	C. P. HALL PARAPLEX G-50
0050	AKROCHEM RETARDER SAX POWDER	0109	C. P. HALL PARAPLEX G-51
0051	AKROCHEM RETROCURE G	0110	C. P. HALL PARAPLEX G-54
0052	AKROCHEM RETROZONE NS	0111	C. P. HALL PARAPLEX G-56
0053	AKROCHEM TBUT LIQUID	0112	C. P. HALL PARAPLEX G-57
0054	AKROCHEM TDEC PELLETS	0113	C. P. HALL PARAPLEX G-62
0055	AKROCHEM TETD POWDER	0114	C. P. HALL PEPTIZER 566
0056	AKROCHEM TMTD POWDER	0115	C. P. HALL PLASTHALL 100
0057	AKROCHEM TMTM POWDER	0116	C. P. HALL PLASTHALL 207 DBES
0058	AKROCHEM ZBED POWDER	0117	C. P. HALL PLASTHALL 220 (DBEEP)
0059	AKROCHEM ZBUDX LIQUID	0118	C. P. HALL PLASTHALL 226-DBEEA

<u>No.</u>	<u>Compound Description</u>
0119	C. P. HALL PLASTHALL 4141
0120	C. P. HALL PLASTHALL 7006
0121	C. P. HALL PLASTHALL 7046
0122	C. P. HALL PLASTHALL 7049
0123	C. P. HALL PLASTHALL 704I
0124	C. P. HALL PLASTHALL 7050
0125	C. P. HALL PLASTHALL 8-10-TM-E
0126	C. P. HALL PLASTHALL 83SS
0127	C. P. HALL PLASTHALL BSA
0128	C. P. HALL PLASTHALL DBEA
0129	C. P. HALL PLASTHALL DBEEG
0130	C. P. HALL PLASTHALL DBEP
0131	C. P. HALL PLASTHALL DIDG
0132	C. P. HALL PLASTHALL DIODD
0133	C. P. HALL PLASTHALL DOSS
0134	C. P. HALL PLASTHALL NODA
0135	C. P. HALL PLASTHALL P-1070
0136	C. P. HALL PLASTHALL P-550
0137	C. P. HALL PLASTHALL P-643
0138	C. P. HALL PLASTHALL P-670
0139	C. P. HALL PLASTHALL P-7035
0140	C. P. HALL PLASTHALL P-7068
0141	C. P. HALL PLASTHALL P-7092
0142	C. P. HALL PLASTHALL R-9
0143	C. P. HALL PLASTHALL TIOTM
0144	C. P. HALL PLASTHALL TOTM
0145	CELANESE ARamid HT
0146	CYANAMID ANTIOXIDANT 2246
0147	CYANAMID ANTIOXIDANT 425
0148	CYANAMID CUPSAC ACCELERATOR
0149	CYANAMID CYANOX 53 ANTIOXIDANT
0150	CYANAMID CYANOX LDTP ANTIOXIDANT
0151	CYANAMID CYANOX STDP ANTIOXIDANT
0152	CYANAMID CYASORB UV 531 LIGHT ABS
0153	CYANAMID CYREZ 933 RESIN
0154	CYANAMID CYREZ 963 RESIN
0155	CYANAMID CYREZ 963 RESIN POWDER C
0156	CYANAMID CYREZ 964 RESIN POWDER C
0157	CYANAMID DOTG DUSTLESS
0158	CYANAMID DPG DUSTLESS
0159	CYANAMID MOTS NO.1 ACCELERATOR
0160	DIAMOND SHAMROCK CHLOROWAX 50
0161	DUPONT ACCELERATOR 552
0162	DUPONT ACCELERATOR 833
0163	DUPONT CAYTUR 21
0164	DUPONT DIAK NO. 1
0165	DUPONT DIAK NO. 2
0166	DUPONT DIAK NO. 4
0167	DUPONT HVA-2
0168	DUPONT PERMALUX
0169	DUPONT POLYAC
0170	DUPONT TERACOL 650
0171	ETHOX 2619
0172	EVANS DILAURYL THIODIPROPINATE
0173	EVANS DISTEARYL THIODIPROPIONATE
0174	EXXON PD 596-25.1
0175	GOODYEAR WING-STAY L
0176	GOODYEAR WING-STAY S
0177	GOODYEAR WING-STAY T
0178	GOODYEAR WING-STAY V
0179	HARWICK EPOLENE N-34-P
0180	HARWICK NATRO-REZ 10
0181	HARWICK NATRO-REZ 25
0182	HARWICK RESINALL CP-25
0183	HARWICK STEARIC ACID F-1000 FLAKE
0184	HARWICK STEARIC ACID F-1500

<u>No.</u>	<u>Compound Description</u>
0185	HARWICK STEARIC ACID F-2000 FLAKE
0186	HARWICK STEARIC ACID F-300 FLAKES
0187	HARWICK ZINC STEARATE H
0188	HERCULES BELRO ROSIN
0189	HERCULES ECHO A
0190	HERCULES PE-200
0191	HERCULES PICCO 6100
0192	INSULCAST RTVS 100
0193	INSULCAST RTVS 11
0194	INSULCAST RTVS 13
0195	INSULCAST RTVS 27-17
0196	INSULCAST RTVS 51
0197	KING PLASTOGEN E
0198	KING REOGEN
0199	MONSANTO A-1
0200	MONSANTO BUTASAN PELLETS
0201	MONSANTO FLECTOL H
0202	MONSANTO FLECTOL ODP
0203	MONSANTO METHASAN POWDER
0204	MONSANTO MONO THIURAD PELLETS
0205	MONSANTO SANTOFLEX 13 PASTILLES
0206	MONSANTO SANTOFLEX IP
0207	MONSANTO SANTONOX
0208	MONSANTO SANTONOX R
0209	MONSANTO SANTOVAR A
0210	MONSANTO SANTOVAR A MILLED
0211	MONSANTO SANTOWHITE 54S
0212	MONSANTO SANTOWHITE MK
0213	MONSANTO SANTOWHITE PC
0214	MONSANTO SANTOWHITE POWDER
0215	MONSANTO THIoTAX MBT (O. T.)
0216	MONSANTO THIURAD PELLETS
0217	PETROLITE WB-10
0218	PETROLITE WB-5
0219	PETROLITE WB-7
0220	QUANTUM EMERSOL 875 ISOTEARIC AC
0221	QUANTUM EMPOL 1010 DIMER ACID
0222	R. T. VANDERBILT AGERITE DPPD
0223	R. T. VANDERBILT AGERITE GELTROL
0224	R. T. VANDERBILT AGERITE HIPAR T
0225	R. T. VANDERBILT AGERITE HP-S
0226	R. T. VANDERBILT AGERITE MA
0227	R. T. VANDERBILT AGERITE NEPA
0228	R. T. VANDERBILT AGERITE RESIN D
0229	R. T. VANDERBILT AGERITE SPAR
0230	R. T. VANDERBILT AGERITE STALITE
0231	R. T. VANDERBILT AGERITE SUPERFLE
0232	R. T. VANDERBILT AGERITE SUPERLIT
0233	R. T. VANDERBILT AGERITE WHITE
0234	R. T. VANDERBILT AGERITE WHITE-WH
0235	R. T. VANDERBILT ALTAX
0236	R. T. VANDERBILT AMAX NO. 1
0237	R. T. VANDERBILT AMYL LEDATE
0238	R. T. VANDERBILT AMYL ZIMATE
0239	R. T. VANDERBILT ANTOZITE 2
0240	R. T. VANDERBILT ANTOZITE 67P
0241	R. T. VANDERBILT BISMATE
0242	R. T. VANDERBILT BUTYL EIGHT
0243	R. T. VANDERBILT BUTYL TUADS
0244	R. T. VANDERBILT BUTYL ZIMATE
0245	R. T. VANDERBILT CAPTAX
0246	R. T. VANDERBILT CURE-RITE 18 PEL
0247	R. T. VANDERBILT DURAX
0248	R. T. VANDERBILT ETHYL CADMATE
0249	R. T. VANDERBILT ETHYL NAMATE
0250	R. T. VANDERBILT ETHYL SELENAC

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
0251	R. T. VANDERBILT ETHYL TELLURAC	0301	R. T. VANDERBILT VANOX MTI
0252	R. T. VANDERBILT ETHYL TUADS RODF	0302	R. T. VANDERBILT VANOX SKT
0253	R. T. VANDERBILT ETHYL ZIMATE	0303	R. T. VANDERBILT VANOX SN-1
0254	R. T. VANDERBILT ISOBUTYL NICLATE	0304	R. T. VANDERBILT VANOX ZMTI
0255	R. T. VANDERBILT METHYL CUMATE	0305	R. T. VANDERBILT VANOX ZS
0256	R. T. VANDERBILT METHYL LEDATE	0306	R. T. VANDERBILT VANPLAST PL
0257	R. T. VANDERBILT METHYL NICLATE	0307	R. T. VANDERBILT VAROX 118
0258	R. T. VANDERBILT METHYL SELENAC	0308	R. T. VANDERBILT VAROX 130
0259	R. T. VANDERBILT METHYL TUADS POW	0309	R. T. VANDERBILT VAROX 231
0260	R. T. VANDERBILT METHYL ZIMATE	0310	R. T. VANDERBILT VAROX 231-XL
0261	R. T. VANDERBILT MORFAX	0311	R. T. VANDERBILT VAROX DBPH
0262	R. T. VANDERBILT OCTOATE Z	0312	R. T. VANDERBILT VAROX DBPH-50
0263	R. T. VANDERBILT PROPYL ZITHATE	0313	R. T. VANDERBILT VAROX DCP-40C
0264	R. T. VANDERBILT ROTAX	0314	R. T. VANDERBILT VAROX DCP-40KE
0265	R. T. VANDERBILT SETSIT 104	0315	R. T. VANDERBILT VAROX VC-40KE
0266	R. T. VANDERBILT SETSIT 9	0316	R. T. VANDERBILT VAROX VC-R
0267	R. T. VANDERBILT SULFADS	0317	R. T. VANDERBILT ZETAX
0268	R. T. VANDERBILT THIAE EF-2	0318	STRUK-CHEM BONDOGEN E
0269	R. T. VANDERBILT UNADS	0319	STRUK-CHEM CBS-O
0270	R. T. VANDERBILT VANAX 552	0320	STRUK-CHEM CDMC-O
0271	R. T. VANDERBILT VANAX 808	0321	STRUK-CHEM MBT-O
0272	R. T. VANDERBILT VANAX 829	0322	STRUK-CHEM MBTS-O
0273	R. T. VANDERBILT VANAX 833	0323	STRUK-CHEM MBTS-P
0274	R. T. VANDERBILT VANAX A	0324	STRUK-CHEM NDBC-O
0275	R. T. VANDERBILT VANAX DOTG	0325	STRUK-CHEM TDEC-O
0276	R. T. VANDERBILT VANAX DPG	0326	STRUK-CHEM TM-O
0277	R. T. VANDERBILT VANAX MBM	0327	STRUK-CHEM TMTD-P
0278	R. T. VANDERBILT VANAX NP	0328	STRUK-CHEM ZDBC-O
0279	R. T. VANDERBILT VANAX NS	0329	STRUK-CHEM ZDEC-P
0280	R. T. VANDERBILT VANAX PML	0330	STRUK-CHEM ZDMC-O
0281	R. T. VANDERBILT VANAX PY	0331	STRUK-CHEM ZDMC-P
0282	R. T. VANDERBILT VANFRE DFL	0332	STRUK-CHEM ZMBT-PQ
0283	R. T. VANDERBILT VANFRE HYP	0333	STRUKTOL A-WAX
0284	R. T. VANDERBILT VANFRE IL-1	0334	TENNECO NUOSTABE V-1298
0285	R. T. VANDERBILT VANFRE M	0335	UNIROYAL ARAZATE 1254
0286	R. T. VANDERBILT VANFRE UN	0336	UNIROYAL BEUTENE
0287	R. T. VANDERBILT VANLUBE 81	0337	UNIROYAL BLE-25
0289	R. T. VANDERBILT VANOX 102	0338	UNIROYAL CPB ACCELERATOR
0288	R. T. VANDERBILT VANOX 12	0339	UNIROYAL DBA ACCELERATOR
0290	R. T. VANDERBILT VANOX 1290	0340	UNIROYAL ETHAZATE (C-222)
0291	R. T. VANDERBILT VANOX 2	0341	UNIROYAL FLEXZONE 6H POWDER
0292	R. T. VANDERBILT VANOX 2-AZ	0342	UNIROYAL HEPTEN BASE
0293	R. T. VANDERBILT VANOX 3C	0343	UNIROYAL NAUGARD 451
0294	R. T. VANDERBILT VANOX 6H	0344	UNIROYAL NAUGARD SP
0295	R. T. VANDERBILT VANOX AM	0345	UNIROYAL NAUGAWHITE
0296	R. T. VANDERBILT VANOX AT	0346	UNIROYAL ROYALAC 133
0297	R. T. VANDERBILT VANOX GT	0347	UNIROYAL ROYALAC 136 LIQUID
0298	R. T. VANDERBILT VANOX K	0348	UNIROYAL ROYALAC 136 POWDER
0299	R. T. VANDERBILT VANOX L	0349	UNIROYAL TRIMENE BASE
0300	R. T. VANDERBILT VANOX MBPC	0350	WITCO 80Z MARK OTM