

Forensics by Raman Spectral Library

Index of Compounds

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
116	1-phenylcyclohexamine HCl 464	13	d,l amphetamine sulphate 316
152	2,4,5 - trimethoxyamphetamine HCl 515	83	D2 Bromo LSD 408
151	2,4,6 trimethoxyamphetamine HCl 516	15	d-amphetamine.hcl 314
150	3,4,5 trimethoxyamphetamine HCl (TMA) 517	43	demoxepam 358
113	5-(p-methylphenyl)-5-phenyl hydantion 472	42	dextromethorphan 359
163	5,5 diphenylhydantoin 544	41	diacetylmorphine HCl 360
114	5-methyl-5-phenylhydantion 471	56	diallylbarbituric acid 361
161	Acetaminophen	55	diazepam 362
1	Acetaminophen 301	54	didrate 363
8	acetanilide 302	53	diethylstilbestrol 365
7	acetylcodeine 304	52	diethyltryptamine HCl 366
6	allylcyclopentenyl Barbituric acid 307	64	dimethyltryptamine furate 371
102	alpha methyl fentanyl HCl 427	63	diphenoxylate.HCl 372
5	alphaprodine 308	62	dipropyltryptamine.HCl 373
4	alphenal 309	61	disulfiram 374
3	alprazolam 310	51	DL -2, -5 dimethoxyamphetamine.HCl 368
2	aminoantipyridine (-4) 311	50	DL 2,5 dimethoxy-4-ethylamphetamine.HCl 369
9	amitriptyline.HCl 312	49	DL 2,5 dimethoxy-4-methylamphetamine 370
16	amobarbital 313	122	DL-propranolol HCl 480
12	antipyridine 317	162	doxylamine succinate 546
11	aprobarbital 319	124	D-propoxyphene HCl 478
10	aspartame apm 321	60	dyphylline 375
24	atabrine 322	57	ethinamate 380
23	atropine sulphate 323	72	ethosuximide 381
22	barbital 324	71	ethylmorphine HCl 382
21	barbituric acid 325	70	etonitazene 383
20	benzocaine 326	69	fenfluramine HCl 384
19	benzoylecgonine tetrahydrate 327	68	fentanylcitrate 386
18	benzphetamine.HCl 328	67	flurazepam dihydrochloride 389
17	bromoazepam 330	66	furosemide 390
32	butabarbital 332	65	glutethimide 391
31	butacaine 333	80	halazepam 392
30	butalbital 334	79	haloperidol 393
29	butethal 335	78	hexobarbital 395
28	butylvinyl 336	77	hydrocodone bitartrate 397
27	caffeine 337	76	hydromorphone 398
26	cannabidiol 338	75	hydroxyamphetamine HBr 399
25	cannabinol 339	74	ibogaine HCl 400
40	carbamazepine 340	73	ibuprofen 401
39	carbromal 341	165	iminostilbene 539
146	carisoprodol 525	169	Iodine
38	chlordiazepoxide 345	88	Ketamine HCl 402
34	chloromazine 349	59	l-ecgonine HCl 376
37	chloroprocaine 346	58	l-ephedine 378
36	chloroquine phosphate 347	86	levorphanol tartrate 404
35	chlorothiazide 348	87	levoxypropoxyphene napsylate 403
33	cholesterol (5(6)-cholesten-3-ol) 350	85	lidocaine 405
48	cimetidine 351	111	L-Norpseudoephedrine HCl 445
47	clonazepam 352	84	lorazepam 407
46	cocaine.HCl 354	164	loxapine succinate 541
45	codeine 355	136	L-psuedoephedrine HCl 482
44	cyclazocine 357	82	lysergic acid diethylamide tartate LSD 410
14	d amphetamine sulphate 315	81	MDE HCl 412
90	d methamphetamine 422	96	meperidine HCl 415

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
147	mephentermine sulphate 524	125	procaine HCL 477
95	mephobarbital 416	155	prochlorperazine edyisylate 533
94	mepivacaine HCl 417	154	promazine HCl 534
93	meproamate 418	153	promethazine HCl 535
92	mescaline HCl 419	123	propoxyphene Napsylate 479
91	Methadone HCl 420	157	propyl hexedrine HCl 531
89	methapyriline HCl 423	121	propylamphetamine HCl 481
104	methaqualone 424	168	protriptyline 536
103	methsuximide 426	135	psilocybin 485
101	methylphenidate HCl 431	134	quinine HCl 487
100	morphine monohydrate 435	172	red meth in cap tube
159	N,N dimethylamphetamine 528	171	red phosphorus in DEA bottle
99	nalorphine 436	173	red street methamphetamine
98	naltrexone HCl 437	132	scopolamine HBr 490
158	niacinamide/pyridoxine.HCl/Inositol 530	145	secondary methadone metabolite HCl 526
97	nitrazepam 440	133	sodium saccharin 489
112	N-Normorphine HCl 444	131	strychnine 493
110	Nortriptyline HCl 446	130	talbutal 497
109	PCP Morpholine Analog HCl (1-1-phynyl cycloheyl morpholine HCl 450	129	TCP HCl 1-(1-2-thicnyl) cyclohexcylpiperidine HCl 498
108	PCP N-ethyl Analog HCl (N-ethyl-I-phenylcyclohexylamine HCl) 451	144	TCP Morpholine Analog HCl [1-(1-2-thicnyl)cyclohexyl morpholine HCl] 499
107	pentazocine 454	143	TCP Pyrolidine Analog HCl 500
106	pentobarbital 455	142	temazepam 501
174	PET Ether	141	tetracaine 503
105	phenacetin 456	140	thebaine alkaloid 508
120	phenazocine HBr 457	139	Theophylline 509
119	phendimetrazine HCl 459	138	thiamylal 511
117	phenobarbital 462	137	triazolam 514
148	phentermine HCl 523	167	trifluoperazine dihydrochloride 537
115	phenylephrine HCl 470	166	trifupromazine HCl 538
118	phenylmetrazine HCl 461	160	trimipramine maleate 527
128	Phenylpropanolamine HCl 473	149	tripelennamine HCl 518
127	prazepam 475	175	yellow (normal) color street methamphetamine in glass tube
156	primidone 532	170	yellow meth in cap tube
126	procaine amide HCl 476		