

Near-IR Pharmaceuticals Spectral Library

Index of Compounds

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
61	"Bismuth gallate, basic"	54	Barbital sodium
59	"Bismuth tribromphenate, basic"	55	Bentonite
70	"Calcium phosphate, dibasic (Calcium hydrogen phosphate)"	10	Benzoic acid
89	"Cellulose, microcrystalline (Avicel) "	56	Bergamot oil
99	"Codeine phosphate, hemidryate"	57	Betacare
155	"Glucose (Dextrose), anhydrous"	58	Bismuth subnitrate
159	"Glycyl-L-tyrosine, dihydrate"	60	Bismuth tribromphenate
200	"L-Arginine, basic"	116	Bisulepinium
337	"Oxidized potato starch, acetylester"	117	Bisulepinium chloride
290	"Paraffin, hard"	11	Boric acid
313	"Povidone, insoluble (Kollidon chloride)"	374	Brilliant green
261	"Sodium carbonate, anhydrous"	63	Bromvaletone
269	"Sodium citrate, acid"	64	Bronopol
265	"Sodium citrate, dihydrate"	101	Caffeine
266	"Sodium dihydrogen phosphate (Sodium phosphate, monobasic)"	102	Caffeine and sodium benzoate
276	"Sodium sulfate, anhydrous"	100	Caffeine citrate
346	"Sulfur, colloidal"	65	Calcium acetate
351	"Turpentine oil, rectified"	66	Calcium carbonate
370	"Valerian, solid extract"	71	Calcium chloride
79	[1-(Ethoxycarbonyl)pentadecyl]trimethylammonium bromide	72	Calcium chloride hexahydrate
1	Acesulfame-K	67	Calcium dobesilate
289	Acetaminophen	68	Calcium formate
288	Acetaminophen (Paracetamol)	69	Calcium gluconate
2	Acetazolamide	73	Calcium lactate
3	Acetylcysteine	74	Calcium pantothenate
5	Acetylsalicylic acid	75	Calcium phosphate (Tricalcium phosphate)
4	Acetylytyrosine	76	Calcium stearate
29	Acriflavine	77	Camphor
30	Adeps Solidus	80	Carbomer 940
6	Adipic acid - (from German adipinsaure)	81	Carboxycellulose calcium (Traumacel)
31	Aesculine	83	Carmellose
32	Agar	262	Casein sodium
132	Agrimony extract	325	Castor oil
35	Alprazolam	87	Cellacefate
36	Aluminum monostearate	88	Cellulose (Perlosa SF)
37	Amaranth	34	Cetostearyl alcohol
7	Aminoacetic acid	17	Chenodeoxycholic acid
40	Aminophylline	174	Chloral hydrate
39	Aminopyrine	176	Chloramphenicol
41	Amitriptyline hydrochloride	175	Chloramphenicol palmitate
163	Ammoniated mercury (Mercuric ammonium chloride)	177	Chlorhexidine dihydrochloride
42	Ammonium acetate	178	Chloroxine
43	Ammonium bromide	179	Chlorpromazine hydrochloride
44	Ammonium chloride	180	Chlorprothixene hydrochloride
45	Amylopectin	181	Chlorthalidone
133	Angelica extract	182	Cholesterol
46	Anise oil	183	Choline tartrate
8	Ascorbic acid (Vitamin C)	94	Cinnamon oil
49	Aspartame	95	Ciprofloxacin
9	Aspartic acid	12	Citric acid
50	Atropine sulfate	13	Citric acid monohydrate
52	Bacitracin zinc	97	Citronella oil
53	Barbital	38	Clohexanol hydrochloride
		98	Clopidamide

<u>No.</u>	<u>Compound Description</u>
86	Clove oil
192	Cod liver oil
103	Collodion
328	Congo red
373	Copovidone
104	Coriander oil
253	Crystal violet (Methylrosaniline chloride)
105	Cyanocobalamin (Vitamin B12)
14	Cyanuric acid
106	Cysteine
107	Dexamethasone acetate
108	Dextran 41
109	Dextran 70
93	Dibucaine hydrochloride
110	Dibutyl phthalate
111	Diclofenac sodium
112	Digoxin
113	Dihydroxypropyladenine
114	Diltiazem hydrochloride
115	Dimethicone
118	Dithranol (Anthralin)
119	Dopamine
120	Dosulepin (Dothiepin)
121	Doxycycline
142	Elder extract
122	Enocyaninum E164
123	Ephedrine hydrochloride
124	Epinephrine bitartrate
125	Ergotamine tartrate
126	Ethacridine lactate
127	Ethyl biscoumacetate
128	Etofylline
129	Eucalyptus oil
131	Explotab
144	Famotidine
148	Fennel oil
145	Fenofibrate
205	Flax oil
146	Flunitrazepam
147	Fluorescein
15	Folic acid
149	Fuchsin acid
151	Gelatin
152	Gelatin (180)
153	Gelatin (Animal)
150	Geranium oil
154	Glucose (Dextrose)
156	Glucose (Dextrose) monohydrate
16	Glutamic acid
157	Glyceryl monostearate
160	Guaiaphenesin
78	Hard gelatin capsules
135	Hawthorne extract
162	Homatropine hydrobromide
138	Hops extract
164	Hydrocortisone acetate
165	Hydroxymethylcellulose
166	Hymecromone
167	Hypromellose
168	Hypromellose (4000)

<u>No.</u>	<u>Compound Description</u>
184	Ibuprofen
185	Indapamide hemihydrate
186	Indigo carmine
187	Indomethacin
188	Inositol
189	Iodoform
18	Ioxitalamic acid
190	Ipecac extract
191	Isosorbide-5-mononitrate
62	Kaolin (Heavy Kaolin)
197	Kebuzone
19	Lactic acid
333	Lactose
334	Lactose (200M)
335	Lactose (Lactosum 100)
336	Lactose (Lactosum 200)
198	L-Alanine
91	Lanolin
201	L-Arginine
199	L-Arginine hydrochloride
139	Lavender extract
202	Lavender oil
203	L-Cystine
140	Lemon balm extract
96	Lemon oil
204	L-Histidine
206	Licorice fluid extract
207	L-Isoleucine
208	L-Leucine
209	L-Ornithine hydrochloride
210	L-Phenylalanine
211	L-Proline
212	L-Serine
213	L-Threonine
214	L-Tryptophan
215	L-Tyrosine
216	L-Valine
217	Lycatab PGS
218	Lysine acetate
219	Lysine hydrochloride
220	Macrogol 1500
221	Macrogol 300
222	Macrogol 4000
223	Macrogol 6000
224	Magnesium carbonate
227	Magnesium chloride
228	Magnesium chloride hexahydrate
225	Magnesium citrate
226	Magnesium formate
229	Magnesium lactate
230	Magnesium lactate dihydrate
231	Magnesium stearate
232	Magnesium sulfate
20	Malic acid
233	Maltose
234	Manganese sulfate
235	Mannitol
137	Meadowsweet extract
238	Menthol
239	Mephenoxalone

<u>No.</u>	<u>Compound Description</u>	<u>No.</u>	<u>Compound Description</u>
240	Meractamine chloride	236	Pregelatinised maize starch
241	Mesalazine	315	Procaine hydrochloride
130	Methacrylic acid copolymer type L	316	Propafenone
242	Methenamine	317	Propyl gallate
243	Methionine	318	Propylparaben
244	Methylcellulose (450)	319	Propyphenazone
249	Methylcellulose (Methoce K15)	320	Pyridoxine hydrochloride (Vitamin B6)
245	Methylcellulose (Methocel E15)	171	Quinidine
246	Methylcellulose (Methocel E3)	169	Quinidine hydrochloride
247	Methylcellulose (Methocel E5)	170	Quinidine sulfate
251	Methylcellulose (Methocel E50)	172	Quinine hydrochloride
248	Methylcellulose (Methocel K100)	173	Quinine sulfate
250	Methylcellulose (Methocel K4)	321	Ranitidine hydrochloride
254	Methylene blue (Tetramethylthionine chloride)	322	Reserpine
252	Methylparaben	323	Resorcinol
255	Metipranolol	324	Riboflavin (Vitamin B2)
256	Metronidazole	285	Rice starch
257	Myrrh tincture	326	Rosemary oil
258	Nafronyl oxalate = Naftidrofuryl hydrogen oxalate	327	Roxithromycin
259	Naloxone	329	Rutin
279	Neomycin sulfate	330	Saccharin sodium
143	Nettle extract	22	Salicylic acid
280	Nicotinamide	306	Saturated long chain monoglycerides
21	Nicotinic acid	134	Shepherd's Purse extract
281	Nitrofurantoin	136	Siberean ginseng extract
282	Ofloxacin	260	Sodium benzoate
283	Olive oil	263	Sodium cetyl sulfate
33	Opaspray K-1-7000	264	Sodium citrate
51	Orange oil	267	Sodium dichlorisocyanurate
284	Ornidazole	268	Sodium edetate
286	Oxiconazole nitrate	271	Sodium iodide
287	Papaverine hydrochloride	272	Sodium lauryl sulfate
291	Pectin (Citrus 106)	273	Sodium perborate
141	Peppermint extract	274	Sodium salicylate
237	Peppermint oil	82	Sodium salt of carboxymethyl starch
292	Phenacetin	84	Sodium salt of carmellose
293	Phenazone (Antipyrine)	85	Sodium salt of carmellose
294	Phenazone and caffeine citrate	341	Sodium stearyl fumarate
295	Phenobarbital	275	Sodium sulfate
296	Phenobarbital sodium	270	Sodium sulfhydrate
297	Phenol	277	Sodium tetraborate (Borax)
299	Phenyl salicylate	278	Sodium thiosulfate
298	Phenylmercuric borate	338	Sorbitan stearate
300	Phthalylsulphathizaole	339	Sorbitol
301	Pilocarpine hydrochloride	92	Spermaceti
302	Pine oil	23	Stearic acid
303	Piroxicam	340	Stearin
304	Pitofenone hydrochloride	158	Stearin (glyceryl tristearate)
305	Podophyllum resin	342	Streptomycin sulfate
307	Polysorbate	331	Sucrose
308	Polysorbate 20	332	Sucrose powder
309	Polysorbate 80	343	Sulfadimidine sodium
193	Potassium acetate	24	Sulfanilic acid
194	Potassium citrate	344	Sulfathiazole
195	Potassium citrate monohydrate	345	Sulfoguaiacole
196	Potassium sorbate	25	Sulfosalicylic acid
310	Povidone 25 (Kollidon 25)	347	Sulpiride
311	Povidone 30 (Kollidon 30)	161	Sunflower oil
312	Povidone 90 (Kollidon 90)	348	Talc
314	Prazosin hydrochloride	349	Tannin

<u>No.</u>	<u>Compound Description</u>
47	Targesin
48	Targesin with borax
26	Tartaric acid
352	Terfenadine
353	Tetracaine hydrochloride
354	Tetracycline hydrochloride
355	Theophylline
356	Thiamine hydrochloride (Vitamin B1)
357	Thioridazine
358	Thyme oil
359	Thymol
27	Tiaprofenic acid
360	Tocopheryl acetate (50%) CWS/F (Vitamin E)
361	Tragacanth
362	Tramadol hydrochloride
363	Tridecanamine undecylenate
364	Triethyl citrate
365	Trimecaine hydrochloride
366	Trimethoprim

<u>No.</u>	<u>Compound Description</u>
368	Troloxerutin
350	Turpentine oil
369	Urea
28	Ursodeoxycholic acid
371	Valarian tincture
372	Verapamil hydrochloride
375	Wax
367	Wheat flour
90	White beeswax
376	WMK (Watermelon Keton)
377	Xanthinol nicotinate
378	Xylitol
379	Xylose
380	Yohimbine hydrochloride
385	Zinc carbonate
381	Zinc lactate
382	Zinc stearate
383	Zinc sulfate
384	Zinc undecylenate