



ThermoFisher
SCIENTIFIC
 275 AIKEN ROAD
 ASHEVILLE, NC 28804

THE INFORMATION CONTAINED HEREIN IS THE PROPRIETARY DATA OF THERMO FISHER SCIENTIFIC. IT IS NOT TO BE REPRODUCED OR DISCLOSED IN WHOLE OR IN PART WITHOUT PRIOR WRITTEN CONSENT OF THERMO FISHER SCIENTIFIC. DO NOT SCALE THIS DRAWING.

TITLE **FREEZER**
SOLID SS SINGLE DOOR
25CuFT

3rd ANGLE PROJECTION 

DWG. NO.

SIZE **S** SHEET 1 OF 2

MF25SS-SAE

REV.	ECN #	DATE	DESCRIPTION
A	60619	2011-08-22	PORTHOLE LOCATION 64.5 WAS 52.0 & LABEL LOCATION CHANGED
-	60088	2011-02-10	INITIAL RELEASE
REVISIONS			

GENERAL SPECIFICATIONS

1. EXTERIOR FINISH: STAINLESS STEEL FRONT, PAINTED GRAY SIDES.
2. EXTERIOR DIMENSIONS:
WIDTH 679.5mm(26.75") DEPTH 857.3mm(33.75") HEIGHT 2070.1mm(81.5")
3. INTERIOR FINISH: STAINLESS STEEL
4. INTERIOR DIMENSIONS:
WIDTH 558.8mm(22") DEPTH 711.2mm(28") HEIGHT 1524mm(60")
5. INSULATION: FOAMED IN PLACE, CFC AND HCFC-FREE POLYURETHANE
6. GASKET: MAGNETIC
7. DOOR: SOLID STAINLESS STEEL DOOR SINGLE, KEY LOCK
8. SHELVES: GRAY-3 WIRE, EPOXY COATED, ADJUSTABLE IN 1/2" INCREMENTS.
9. CASTERS: 4 STEM MOUNT
10. CONTROLLER: DIGITAL, FACTORY PRESET TO -30°C (-22°F)
11. DEFROST : AUTOMATIC
12. COMPRESSOR: 3/4 HP, REFERIGERANT R404A
13. TEMPERATURE RANGE: -30° TO -12°C
14. AVERAGE TEMPERATURE STABILITY: ±3°C
15. APPROVALS: UL/cUL
16. ELECTRICAL DATA: 115V 60Hz/10 AMPS
17. PLUG TYPE: NEMA 5-15P
18. TOTAL CAPACITY: 24Cuft
19. SHIPPING WEIGHT: 178KG (392 LBS).

<p>ThermoFisher SCIENTIFIC 275 AIKEN ROAD ASHEVILLE, NC 28804</p>	<p>THE INFORMATION CONTAINED HEREIN IS THE PROPRIETARY DATA OF THERMO FISHER SCIENTIFIC. IT IS NOT TO BE REPRODUCED OR DISCLOSED IN WHOLE OR IN PART WITHOUT PRIOR WRITTEN CONSENT OF THERMO FISHER SCIENTIFIC. DO NOT SCALE THIS DRAWING.</p>												
<p>TITLE FREEZER SOLID SS SINGLE DOOR 25CuFT</p>													
<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 10%; text-align: center;">-</td> <td style="width: 10%; text-align: center;">-</td> <td style="width: 10%; text-align: center;">-</td> <td style="width: 70%; text-align: center;">SEE SHEET 1</td> </tr> <tr> <td style="text-align: center;">REV.</td> <td style="text-align: center;">ECN #</td> <td style="text-align: center;">DATE</td> <td style="text-align: center;">DESCRIPTION</td> </tr> <tr> <td colspan="4" style="text-align: center;">REVISIONS</td> </tr> </table>	-	-	-	SEE SHEET 1	REV.	ECN #	DATE	DESCRIPTION	REVISIONS				<p>3rd ANGLE PROJECTION DWG. NO. MF25SS-SAE</p> <p>SIZE S SHEET 2 OF 2</p>
-	-	-	SEE SHEET 1										
REV.	ECN #	DATE	DESCRIPTION										
REVISIONS													