



Acceleration and Deceleration Profiles

for Thermo Scientific Small Benchtop Centrifuges

Technical Information

50147424-a • 01 / 2015


Thermo
SCIENTIFIC

This document contains acceleration and deceleration profiles for the Thermo Scientific™ Heraeus™ Megafuge™ 8 / 8R, the Thermo Scientific™ Sorvall™ ST 8 / 8R and the Thermo Scientific SL 8 / 8R small benchtop centrifuges.

Please note that there are differences between the maximum speeds of the rotors. The maximum speed is depending on if either a ventilated or a refrigerated centrifuge is used. Details can be found in the specific centrifuge manual and in the rotor manual.


Thermo Scientific TX-150 Rotor

Article No. 75005701




Thermo Scientific M10 Rotor

Article No. 75005706




Thermo Scientific MT-12 Rotor

Article No. 75005600




Thermo Scientific TX-100S Rotor

Article No. 75005704




Thermo Scientific TX-100 Rotor

Article No. 75005705




Thermo Scientific HIGHConic III Rotor

Article No. 75005709




Thermo Scientific 8x50 mL Individually Sealed Rotor

Article No. 75003694




Thermo Scientific CLINIConic Rotor

Article No. 75003623




Thermo Scientific MicroClick 18x5 Rotor

Article No. 75005765




Thermo Scientific MicroClick 30x2 Rotor

Article No. 75005719




Thermo Scientific MicroClick 24x2 Rotor

Article No. 75005715




Thermo Scientific 8x8 PCR Strip Rotor

Article No. 75005720



Thermo Scientific Hematocrit Rotor

Article No. 75005733



Thermo Electron LED GmbH
Zweigniederlassung Osterode
Am Kalkberg, 37520 Osterode am Harz
Germany

thermoscientific.com/centrifuge

© 2015 Thermo Fisher Scientific Inc. All rights reserved.

All other trademarks are the property of Thermo Fisher Scientific Inc. and its subsidiaries.

Specifications, terms and pricing are subject to change. Not all products are available in all countries. Please consult your local sales representative for details.

Shown pictures within the manual are examples and may differ considering the set parameters and language.

United States/Canada +1 866 984 3766

Latin America +1 866 984 3766

Austria +43 1 801 40 0

Belgium +32 53 73 42 41

France +33 2 2803 2180

Germany national toll free 0800 1 536 376

Germany international +49 61 84 90 6000

Italy +39 02 95059 552

Netherlands +31 76 579 55 55

Nordic/Baltic States/CIS +358 9 329 10200

Russia +7 812 703 42 15

Spain/Portugal +34 93 223 09 18

Switzerland +41 44 454 12 22

UK/Ireland +44 870 609 9203

India +91 22 6716 2200

China +800 810 5118 or
+400 650 5118

Japan +81 3 5826 1616

Other Asian Countries +852 2885 4613

Australia +61 39757 4300

New Zealand +64 9 980 6700

Countries not listed +49 6184 90 6000 or
+33 2 2803 2180

Thermo
SCIENTIFIC

Part of Thermo Fisher Scientific