



GENERAL SPECIFICATIONS:

1. EXTERIOR: STAINLESS STEEL FRONT, ALUMINUM ENDS
2. EXTERIOR DIMENSIONS: WIDTH: 26", DEPTH: 35.5", HEIGHT: 82.25"
3. INTERIOR: ALUMINUM
4. INTERIOR DIMENSIONS: WIDTH: 20", DEPTH: 28.75", HEIGHT: 28"
5. INSULATION: FOAMED IN PLACE, CFC AND HCFC-FREE POLYURETHANE
6. GASKET: MAGNETIC
7. DOOR: SOLID STAINLESS STEEL WITH KEY LOCK
8. SHELVES: GRAY-4 WIRE, EPOXY COATED, ADJUSTABLE IN 1/2" INC.
9. CASTERS: STEM MOUNT, QTY 4
10. CONTROL: DIGITAL, FACTORY PRESET TO +4°C (REFRIGERATOR) AND -20°C (FREEZER)
11. DEFROST: AUTOMATIC
12. REFRIG. COMPRESSOR: 1/5 HP, REFRIGERANT R134A
13. FREEZER COMPRESSOR: 1/4 HP, REFRIGERANT R404A
14. TEMP RANGE: REFRIGERATOR: 1C TO 12C; FREEZER: -20C TO 0C
15. AVERAGE TEMP STABILITY: ±3°C
16. ELECTRICAL DATA: 115V 60Hz REF:6.9 AMPS, FRZ:5.4 AMPS
17. PLUG TYPE: 2X NEMA 5-15P
18. TOTAL CAPACITY: 20 CuFt (10 EACH)
19. SHIPPING WEIGHT: 420 lbs.

-	60088	2011-04-28	RELEASE
REV.	ECN#	DATE	DESCRIPTION

REVISION

ThermoFisher SCIENTIFIC 275 AIKEN ROAD ASHEVILLE, NC 28804	THE INFORMATION CONTAINED HEREIN IS THE PROPRIETARY DATA OF THERMO FISHER SCIENTIFIC. IT IS NOT TO BE REPRODUCED OR DISCLOSED IN WHOLE OR IN PART WITHOUT PRIOR WRITTEN CONSENT OF THERMO FISHER SCIENTIFIC. DO NOT SCALE THIS DRAWING.
---	---

TITLE **REFRIGERATOR / FREEZER**
20CuFT

3rd ANGLE PROJECTION		DWG. NO.
SIZE A	SHEET 1 OF 1	MC20SS-SAAE

A-A
SCALE 1 : 16